
Product datasheet





MOUNTING PLATE NSX/CVS/ VIGI/INS 250 V. FIX.TOGGLE

03050

! Discontinued on: 20 Jun 2023

① Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma Pack 250 duct Prisma Prisma G duct Prisma Prisma P cubicle
Installation Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle - width 400 mm depth 400 mm Pack enclosure - width 300 mm
Installed Device	EasyPact: fixed CVS100160 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: toggle - vertical installation ComPact: fixed INS250 - control: direct front rotary handle - vertical installation ComPact: fixed INV100 - control: direct front rotary handle - vertical installation ComPact: fixed INV250 - control: direct front rotary handle - vertical installation ComPact: fixed INV250 - control: direct front rotary handle - vertical installation ComPact: fixed INV250 - control: direct front rotary handle - vertical installation ComPact: fixed NSX100160 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX250 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS100160 with earth leakage protection - control: toggle - vertical installation EasyPact: fixed NSX100160 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX100160 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX100160 without earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX250 without earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX250 without earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX100160 with earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX250 without earth leakage protection - control: toggle - vertical installation

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Poles Description 1 x 3P: fixed INS250 vertical installation 1 x 4P: fixed INS250 vertical installation 1 x 3P: fixed INV250 vertical installation 1 x 4P: fixed INV250 vertical installation 1 x 3P: fixed INV100 vertical installation 1 x 4P: fixed INV100 vertical installation 1 x 3P: fixed INV160 vertical installation 1 x 4P: fixed INV160 vertical installation 1 x 3P: fixed INV200 vertical installation 1 x 4P: fixed INV200 vertical installation 1 x 3P: fixed CVS100...160 vertical installation 1 x 4P: fixed CVS100...160 vertical installation 1 x 3P: fixed CVS250 vertical installation 1 x 4P: fixed CVS250 vertical installation 1 x 3P: fixed NSX100...160 vertical installation 1 x 4P: fixed NSX100...160 vertical installation 1 x 3P: plug-in NSX100...160 vertical installation 1 x 4P: plug-in NSX100...160 vertical installation 1 x 3P: fixed NSX250 vertical installation 1 x 4P: fixed NSX250 vertical installation 1 x 3P: plug-in NSX250 vertical installation 1 x 4P: plug-in NSX250 vertical installation

Condition Of Using Cable Tie

Need additional plate (1M high) when installation of device is in vertical

Number Of Vertical Modules [50 Mm]

- 9 module(s): CVS100...160 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 9 module(s): CVS100...160 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 9 module(s): CVS100...160 without earth leakage protection, direct with long terminal shield in 300 mm WidePack enclosure (cable coming from top or bottom of enclosure)
- 9 module(s): CVS250 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 9 module(s): CVS250 without earth leakage protection, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 9 module(s): CVS250 without earth leakage protection , direct with long terminal shield in 300 mm WidePack enclosure (cable coming from top or bottom of enclosure)
- 9 module(s): INS250, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 9 module(s): INS250, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 9 module(s): INV100, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 9 module(s): INV100, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 9 module(s): INV160, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) $\frac{1}{2} \left(\frac{1}{2} + \frac{1}{2}$
- 9 module(s): INV160, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 9 module(s): INV200, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 9 module(s): INV200, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 9 module(s): INV250, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 9 module(s): INV250, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 9 module(s): NSX100...160 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 9 module(s): NSX100...160 without earth leakage protection, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- $9\ \text{module(s)}\xspace$ NSX100...160 without earth leakage protection , front connection in 400 mm Widecubicle
- 9 module(s): NSX100...160 without earth leakage protection , direct with long terminal shield in 300 mm WidePack enclosure (cable coming from top or bottom of enclosure)
- 9 module(s): NSX250 without earth leakage protection, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 9 module(s): NSX250 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- $9\ \text{module(s):}\ NSX250$ without earth leakage protection , front connection in $400\ \text{mm}$ Widecubicle
- 9 module(s): NSX250 without earth leakage protection, direct with long terminal shield in 300 mm WidePack enclosure (cable coming from top or bottom of enclosure)
- 13 module(s): CVS100...160 with earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
- 13 module(s): CVS100...160 with earth leakage protection, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 13 module(s): CVS250 with earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 13 module(s): CVS250 with earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure) 13 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of
- 13 module(s): NSX100...160 with earth leakage protection, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
- 11 $\text{module}(\mathbf{s})$: NSX100...160 with earth leakage protection , front connection in 400 mm Widecubicle
- 13 module(s): NSX100...160 with earth leakage protection, direct with long terminal shield in 300 mm WidePack enclosure (cable coming from top or bottom of

enclosure)

13 module(s): NSX250 with earth leakage protection, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
13 module(s): NSX250 with earth leakage protection, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
11 module(s): NSX250 with earth leakage protection, front connection in 400 mm Widecubicle

13 module(s): NSX250 with earth leakage protection , direct with long terminal shield in 300 mm WidePack enclosure (cable coming from top or bottom of enclosure)

Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	300 mm
Height	250 mm
Net Weight	0.54 kg

Functional Unit

- 300 mm Prisma G floor-standing duct EasyPact CVS100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G wall-mounted duct EasyPact CVS100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G floor-standing duct EasyPact CVS100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G wall-mounted duct EasyPact CVS100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G floor-standing duct EasyPact CVS250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G wall-mounted duct EasyPact CVS250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G floor-standing duct EasyPact CVS250 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G wall-mounted duct EasyPact CVS250 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS250 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G floor-standing duct ComPact INS250 fixed direct front rotary
- handle vertical 3P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G wall-mounted duct ComPact INS250 fixed direct front rotary
- handle vertical 3P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G floor-standing duct ComPact INS250 fixed direct front rotary
- handle vertical 4P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G wall-mounted duct ComPact INS250 fixed direct front rotary
- handle vertical 4P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G floor-standing duct ComPact INV100 fixed direct front rotary
- handle vertical 3P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G wall-mounted duct ComPact INV100 fixed direct front rotary
- handle vertical 3P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G floor-standing duct ComPact INV100 fixed direct front rotary
- handle vertical 4P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G wall-mounted duct ComPact INV100 fixed direct front rotary
- handle vertical 4P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G floor-standing duct ComPact INV160 fixed direct front rotary
- handle vertical 3P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G wall-mounted duct ComPact INV160 fixed direct front rotary
- handle vertical 3P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G floor-standing duct ComPact INV160 fixed direct front rotary
- handle vertical 4P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G wall-mounted duct ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 203 mm
- 300 mm Prisma G floor-standing duct ComPact INV200 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 203 mm
- 300 mm Prisma G wall-mounted duct ComPact INV200 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 203 mm
- 300 mm Prisma G floor-standing duct ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 203 mm
- 300 mm Prisma G wall-mounted duct ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 203 mm
- 300 mm Prisma G floor-standing duct ComPact INV250 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 203 mm
- 300 mm Prisma G wall-mounted duct ComPact INV250 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 203 mm
- 300 mm Prisma G floor-standing duct ComPact INV250 fixed direct front rotary
- handle vertical 4P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G wall-mounted duct ComPact INV250 fixed direct front rotary
- handle vertical 4P 1 direct with long terminal shield 9 203 mm 300 mm Prisma G floor-standing duct ComPact NSX100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G wall-mounted duct ComPact NSX100...160 without fixed toggle
- vertical 3P 1 direct with long terminal shield 9 178 mm 300 mm Prisma G floor-standing duct ComPact NSX100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm
- 300 mm Prisma G wall-mounted duct ComPact NSX100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm
- 400 mm 400 mm Prisma P cubicle ComPact NSX100...160 without fixed toggle vertical 3P 1 front connection 9 178 mm
- 400~mm 400~mm Prisma P cubicle ComPact NSX100...160 without fixed toggle vertical 4P 1 front connection 9 178 mm
- 400 mm 400 mm Prisma P cubicle ComPact NSX100...160 without plug-in toggle vertical 3P 1 front connection 9 178 mm
- 400 mm 400 mm Prisma P cubicle ComPact NSX100...160 without plug-in toggle vertical 4P 1 front connection 9 178 mm

300 mm Prisma Pack 250 Pack enclosure ComPact NSX100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm

300 mm Prisma Pack 250 Pack enclosure ComPact NSX100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm

300 mm Prisma G floor-standing duct ComPact NSX250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm

300 mm Prisma G wall-mounted duct ComPact NSX250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm

300 mm Prisma G floor-standing duct ComPact NSX250 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm

300 mm Prisma G wall-mounted duct ComPact NSX250 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm

400 mm 400 mm Prisma P cubicle ComPact NSX250 without fixed toggle vertical 3P 1 front connection 9 178 mm

400 mm 400 mm Prisma P cubicle ComPact NSX250 without fixed toggle vertical 4P 1 front connection 9 178 mm

 $400~\rm mm$ $400~\rm mm$ Prisma P cubicle ComPact NSX250 without plug-in toggle vertical 3P 1 front connection 9 178 mm

400~mm 400~mm Prisma P cubicle ComPact NSX250 without plug-in toggle vertical 4P 1 front connection 9 178 mm

300 mm Prisma Pack 250 Pack enclosure ComPact NSX250 without fixed toggle vertical 3P 1 direct with long terminal shield 9 178 mm

300 mm Prisma Pack 250 Pack enclosure ComPact NSX250 without fixed toggle vertical 4P 1 direct with long terminal shield 9 178 mm

300 mm Prisma G floor-standing duct EasyPact CVS100...160 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G wall-mounted duct EasyPact CVS100...160 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G floor-standing duct EasyPact CVS100...160 with fixed toggle vertical 4P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G wall-mounted duct EasyPact CVS100...160 with fixed toggle vertical 4P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G floor-standing duct EasyPact CVS250 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G wall-mounted duct EasyPact CVS250 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

1 direct with long terminal shield 13 278 mm 300 mm Prisma G floor-standing duct EasyPact CVS250 with fixed toggle vertical 4P

1 direct with long terminal shield 13 278 mm 300 mm Prisma G wall-mounted duct EasyPact CVS250 with fixed toggle vertical 4P

1 direct with long terminal shield 13 278 mm 300 mm Prisma G floor-standing duct ComPact NSX100...160 with fixed toggle

vertical 3P 1 direct with long terminal shield 13 278 mm 300 mm Prisma G wall-mounted duct ComPact NSX100...160 with fixed toggle

and mm Prisma G wall-mounted duct ComPact NSX100...160 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G floor-standing duct ComPact NSX100...160 with fixed toggle vertical 4P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G wall-mounted duct ComPact NSX100...160 with fixed toggle vertical 4P 1 direct with long terminal shield 13 278 mm

400 mm 400 mm Prisma P cubicle ComPact NSX100...160 with fixed toggle vertical 3P 1 front connection 11 278 mm

400 mm 400 mm Prisma P cubicle ComPact NSX100...160 with fixed toggle vertical 4P 1 front connection 11 278 mm

400~mm 400~mm Prisma P cubicle ComPact NSX100...160 with plug-in toggle vertical 3P 1 front connection 11 278 mm

400~mm 400~mm Prisma P cubicle ComPact NSX100...160 with plug-in toggle vertical 4P 1 front connection 11 278 mm

300 mm Prisma Pack 250 Pack enclosure ComPact NSX100...160 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

300~mm Prisma Pack 250 Pack enclosure ComPact NSX100...160 with fixed toggle vertical 4P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G floor-standing duct ComPact NSX250 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G wall-mounted duct ComPact NSX250 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G floor-standing duct ComPact NSX250 with fixed toggle vertical 4P 1 direct with long terminal shield 13 278 mm

300 mm Prisma G wall-mounted duct ComPact NSX250 with fixed toggle vertical 4P 1 direct with long terminal shield 13 278 mm

400 mm 400 mm Prisma P cubicle ComPact NSX250 with fixed toggle vertical 3P 1 front connection 11 278 mm

400 mm 400 mm Prisma P cubicle ComPact NSX250 with fixed toggle vertical 4P 1 front connection 11 278 mm

400~mm 400~mm Prisma P cubicle ComPact NSX250 with plug-in toggle vertical 3P 1 front connection 11 278 mm

400 mm 400 mm Prisma P cubicle ComPact NSX250 with plug-in toggle vertical 4P 1 front connection 11 278 mm

300 mm Prisma Pack 250 Pack enclosure ComPact NSX250 with fixed toggle vertical 3P 1 direct with long terminal shield 13 278 mm

300 mm Prisma Pack 250 Pack enclosure ComPact NSX250 with fixed toggle vertical 4P 1 direct with long terminal shield 13 278 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	16.000 cm
Package 1 Length	22.000 cm
Package 1 Weight	600.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	30
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	18.703 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	240
Package 3 Height	105.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	161.624 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile