# **Product datasheet**

Specifications





## Domae MCB - miniature circuitbreaker - 1P - 20A - C Curve -6000A

17047

! Discontinued on: 20 Nov 2023

! Discontinued

### Main

Range	Domae	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	Domae MCB	
Device Application	Distribution	
Poles Description	1P	
Number Of Protected Poles	1	
[In] Rated Current	20 A	
Network Type	AC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	С	
Breaking Capacity	Icn 6000 A	

### Complementary

Network Frequency	50/60 Hz	
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz	
Magnetic Tripping Limit	510 x ln	
[Ics] Rated Service Breaking Capacity	6000 kA 100 % x Icn conforming to EN/IEC 60898-1	
Contact Position Indicator	Yes	
Control Type	Toggle	
Local Signalling	Fault trip	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
Comb Busbar And Distribution Block Compatibility	YES	
Connection Pitch	18 mm between devices	
9 Mm Pitches	2	
Height	81 mm	
Width	18 mm	
Depth	78.5 mm	
Net Weight	0.095 kg	
Colour	White	

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Mechanical Durability	20000 cycles
Connections - Terminals	Tunnel type terminals (top or bottom) - 125 mm² - rigid Tunnel type terminals (top or bottom) - 116 mm² - flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Without

## **Environment**

Standards	IEC 60068-1 IEC 60898-1 IEC 60529
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4070 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7.4 cm
Package 1 Length	8.5 cm
Package 1 Weight	96.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	144
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	14.904 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	
China Rons Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations