Product datasheet

Specifications





motor-mechanism - MCH - 200..250 V DC

47463

Main

Device Short Name	gear motor MCH
Product Or Component Type	Gear motor mechanism MCH
Device Application	Automatic spring charging
Range Compatibility	Masterpact MasterPact NT circuit breaker
Control Type	Motor mechanism
[Uc] Control Circuit Voltage	200250 V DC
Circuit Breaker Mounting Mode	Drawout

Complementary

Maximum Charging Time	3 s
Maximum Power Consumption In Va	180 VA

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	12.5 cm
Package 1 Length	18.0 cm
Package 1 Weight	843.0 g

Contractual warranty

Warranty

18 months

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information