



# motor-mechanism - MCH - 200..250 V DC

48524

## Main

Device Short Name	gear motor MCH	
Product Or Component Type	Gear motor mechanism MCH	
Device Application	Automatic spring charging	
Range Compatibility	Masterpact MasterPact NW circuit breaker	
Control Type	Motor mechanism	
[Uc] Control Circuit Voltage	200250 V DC	
Circuit Breaker Mounting Mode	Drawout	

## Complementary

Maximum Charging Time	4 s
Maximum Power Consumption In Va	180 VA

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	13.1 cm
Package 1 Length	22.9 cm
Package 1 Weight	1.874 kg

## **Contractual warranty**

Warranty	18 months	

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	