# **Product datasheet**

Specifications





# Acti 9 - Auxiliary contact iOF/ SD+OF - 2OC - AC/DC

A9A26929

- () Discontinued on: 23 Apr 2024
- () To be end-of-service on: 1 Jun 2024

① To be discontinued

#### Main

Range Of Product	Acti9
Product Or Component Type	Double OC or fault contact
Device Short Name	iOF/SD+OF
Signal Contacts Composition	2 C/O
[In] Rated Current	DC-12 1 A at 130 V, DC
	DC-12 1.5 A at 60 V, DC
	DC-12 2 A at 48 V, DC
	DC-12 6 A at 24 V, DC
	AC-12 3 A at 415 V, AC 50/60 Hz
	AC-12 6 A at 240 V, AC 50/60 Hz
9 Mm Pitches	1

### Complementary

[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Local Signalling	Mechanical indicator
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
Height	90 mm
Width	9 mm
Depth	73 mm
Net Weight	43 g
Colour	White
Connections - Terminals	Screw clamp terminal (top and bottom) 2 cable(s) 2.5 mm <sup>2</sup> - rigid Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule Screw clamp terminal (top and bottom) 1 cable(s) 0.52.5 mm <sup>2</sup> - flexible Screw clamp terminal (top and bottom) 1 cable(s) 14 mm <sup>2</sup> - rigid
Wire Stripping Length	10 mm
Tightening Torque	1 N.m

#### Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4085 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	2.400 cm
Package 1 Length	9.200 cm
Package 1 Weight	50.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	27.000 cm
Package 2 Weight	693.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	7.600 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information