

Product datasheet

Specifications



iPRD65r modular surge arrester - 3 poles - 460V - with remote transfer

A9L16558

⚠ Discontinued on: 1 Nov 2020

⚠ Discontinued

Main

Range Of Product	Acti9
Product Name	Acti9 iPRD
Product Or Component Type	Surge arrester with pluggable cartridge
Device Short Name	iPRD
Device Application	Distribution
Standards	EN 61643-11 IEC 61643-11
Product Certifications	CE
Poles Description	3P
Remote Signalling	With
Signal Contacts Composition	1 SD (1 C/O)
Surge Arrester Type	Electrical distribution network
Earthing System	IT

Complementary

Surge Arrester Class Type	Type 2
Surge Arrester Technology	MOV
[Ue] Rated Operational Voltage	400 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 20 kA (L/PE)
[Imax] Maximum Discharge Current	Common mode: 65 kA L/PE
[Uc] Maximum Continuous Operating Voltage	Common mode: 460 V L/PE
Maximum [Up] Voltage Protection Level	Common mode <2 kV type 2 L/PE
Disconnecter Device Type	Associated circuit breaker IC60N 50 A curve C - Icu 10 kA Associated circuit breaker iC60H 50 A curve C - Icu 15 kA Associated circuit breaker NG125N 50 A curve C - Icu 25 kA Associated circuit breaker NG125H 50 A curve C - Icu 36 kA Associated circuit breaker NG125L 50 A curve C - Icu 50 kA
Signalling Circuit Voltage	0.25 A/250 V AC 50/60 Hz
Mounting Mode	Clip-on (DIN rail)
9 Mm Pitches	6
Height	81 mm
Width	54 mm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	69 mm
Net Weight	0.395 kg
Colour	White (RAL 9003)
Connections - Terminals	Tunnel type terminal (downside) 2.5...35 mm² Tunnel type terminal (upside) 2.5...35 mm²
Tightening Torque	2.5 N.m

Environment

Ik Degree Of Protection	IK03 conforming to IEC 62262
Relative Humidity	5...90 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	6 cm
Package 1 Length	8.1 cm
Package 1 Weight	0.448 kg

Contractual warranty

Warranty	18 months
----------	-----------