Product datasheet

Specification





Acti 9 - fuse-disconnector STI - 1 pole + N - 25 A - for fuse 10.3 x 38 mm

A9N15646

Main

| Range | Acti9 |
|---------------------------|-------------------|
| Product Name | Acti9 STI |
| Product Or Component Type | Fuse-disconnector |
| Device Short Name | STI |
| Poles Description | 1P + N |

Complementary

| J | |
|--------------------------------|---|
| [In] Rated Current | 2 A |
| | 4 A |
| | 6 A |
| | 10 A |
| | 16 A |
| | 20 A |
| | 25 A |
| Fuse Curve | AM |
| | GG |
| Fuse Size | 10.3 x 38 mm |
| [Ue] Rated Operational Voltage | 500 V AC |
| [Ui] Rated Insulation Voltage | 500 V AC 50/60 Hz |
| Mounting Mode | Clip-on |
| Mounting Support | DIN rail |
| 9 Mm Pitches | 2 |
| Height | 81 mm |
| Width | 18 mm |
| Depth | 75 mm |
| Colour | White |
| Connections - Terminals | Screw clamp terminals1 cable(s) 0.7510 mm² rigid |
| | Screw clamp terminals1 cable(s) 0.56 mm² flexible |
| | Screw clamp terminals2 cable(s) 0.754 mm² rigid |
| | Screw clamp terminals2 cable(s) 0.56 mm² flexible |
| Wire Stripping Length | 12 mm |
| Tightening Torque | 2 N.m |

Environment

| Standards | IEC 60269-1/2 IEC EN 60947-3 |
|-------------------------|---------------------------------|
| Ip Degree Of Protection | IP20 |

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

| Pollution Degree | 3 |
|---------------------------------------|----------|
| Ambient Air Temperature For Operation | -2060 °C |
| Ambient Air Temperature For Storage | -4080 °C |

Packing Units

| PCE |
|-----------|
| 1 |
| 1.700 cm |
| 7.600 cm |
| 8.000 cm |
| 73.000 g |
| BB1 |
| 12 |
| 2.730 cm |
| 30.000 cm |
| 20.000 cm |
| 927.000 g |
| S03 |
| 144 |
| 30.000 cm |
| 30.000 cm |
| 40.000 cm |
| 11.661 kg |
| |



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc |
|----------|--------------------------------|
| ⊘ | Toxic Heavy Metal Free |
| ⊘ | Mercury Free |
| ⊘ | Rohs Exemption Information Yes |
| Ø | Halogen Free Product |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |