





# APC Easy UPS, 1000VA, Floor/ Wall Mount, 230V, 4x Universal outlets, AVR

BV1000I-MSX

#### Overview

Lead Time Usually in Stock

#### Main

IVIAIII	
Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	600 W
Rated Power In Va	1000 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	BS1363A British
Output Connection Type	4 universal receptacle
Cable Length	1.50 m
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	User manual

#### **Batteries & Runtime**

Efficiency	View Efficiency Graph ☐
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Life	35 year(s)
Replacement Battery	RBC17 ☐
Extended Runtime	0

#### **General**

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No
Ups Size	WS

#### **Physical**

Colour	Black
Height	9.25 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Width	16.05 cm
Depth	30.5 cm
Net Weight	5.7 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

### Input

Network Frequency	50/60 Hz +/- 5 Hz auto-sensing
Input Voltage Limits	170280 V

### Output

Maximum Configurable Power In W	600 W
Output Frequency	50/60 Hz +/- 1 Hz unsynchronised
Ups Type	Line interactive
Wave Type	Stepped approximation to a sinewave
Graph Display	1
Maximum Configurable Power In Va	1000 VA
Transfer Time	6 ms typical : 10 ms maximum

#### **Conformance**

Product Certifications	CE
Standards	EN/IEC 62040-1:2019/A11:2021
	EN/IEC 62040-2:2006/AC:2006
	EN/IEC 62040-2:2018

#### **Environmental**

Ambient Air Temperature For Operation	040 °C
Relative Humidity	090 %
Operating Altitude	06667 ft
Ambient Air Temperature For Storage	-2050 °C
Storage Relative Humidity	090 %
Storage Altitude	0.0015240.00 m
Acoustic Level	40 dBA
Ip Degree Of Protection	IP20

# Communications & Management

Alarm Alarm when on battery : distinctive low battery alarm : overload continuous tone

### **Surge Protection and Filtering**

Surge Energy Rate 156 J

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.7 cm
Package 1 Width	37.3 cm
Package 1 Length	14.3 cm
Package 1 Weight	6 kg
Scc14	10731304344053

### **Contractual warranty**

Warranty 2 years repair or replace

## Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Yes



Energy Efficient Take-back Transparency RoHS/REACh

#### Resource performance

Energy Efficient Product

✓ Take-Back Program Available

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information

30 May 2024