Product datasheet

Specifications





Mita - Cableline 50 - installation trunking - 180Wx52 mm - 3 m

DP3W

Main

Range Of Product	Mita	
Product Name	Cableline 50	
Product Or Component Type	Installation trunking	
Colour Tint	White/grey	
Quantity Per Set	Set of 2	

Complementary

Compartment Partitioning	3 compartments	
Trunking Dimension	180W x 52 mm	
Trunking Material	Plastic	
Front Opening Size	87 mm	
Device Composition	white trunking base grey lid (x 3)	
Fixing Mode	Screw-fixed	
Material With Surface Finish	UPVC (unplasticized polyvinyl chloride)	
Product Compatibility	x 25 mm mounting boxes x 35 mm mounting boxes	
Length	3000 mm	
Height	180 mm	
Width	52 mm	

Environment

Standards	ANSI/TIA/EIA-568-B
	BS 4678-4
	BS 6701
	BS 7671
	BS EN 50174-2
	ISO/IEC 11801
	EN 50173
Ambient Air Temperature For Operation	-560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.200 cm
Package 1 Width	18.000 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 1 Length	100.000 cm	
Package 1 Weight	2.130 kg	
Unit Type Of Package 2	CAR	
Number Of Units In Package 2	6	
Package 2 Height	10.800 cm	
Package 2 Width	18.500 cm	
Package 2 Length	302.000 cm	
Package 2 Weight	12.790 kg	
Unit Type Of Package 3	PAL	
Number Of Units In Package 3	432	
Package 3 Height	140.000 cm	
Package 3 Width	300.000 cm	
Package 3 Length	ength 120.000 cm	
Package 3 Weight	995.880 kg	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations