

Product datasheet

Specifications



32A Double Pole Switch with White LED, White

E3031DR32_EWWW

Main

Range	Neo
Wiring Device Mounting	Flush Surface
Switch Function	2-pole
Switch Application	Switch
Load Type	Incandescent lamp Resistive Inductive
Bulb Type	LED (white)
Colour Tint	White

Complementary

Rated Current	32 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang
Material	Polycarbonate: plastic part
Clamping Connection Capacity	1 x 23 mm ² for solid cable(s) 1 x 23 mm ² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	16.8 mm
Depth	28.3 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	8.6 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.6 cm
Package 1 Weight	75 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	1.94 cm
Package 2 Weight	750 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	20.5 cm
Package 3 Width	41.5 cm
Package 3 Length	50 cm
Package 3 Weight	7500 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
<hr/>		
Eu Rohs Directive		Compliant EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
<hr/>		