Product datasheet

Specifications



45A 250V Double Pole Cooker Switch with Blue LED, Grey silver

E3031DR45-EBGS

() Discontinued on: 20 Jun 2023

① Discontinued

Main

Range	Neo
Product Or Component Type	Control switch
Device Application	Control
Wiring Device Mounting	Surface Flush
Switch Function	2-pole
Switch Application	Switch
Load Type	Incandescent lamp Inductive Resistive
Bulb Type	LED (blue)
Colour Tint	Grey silver

Complementary

Rated Current	45 A at 250 V AC 50/60 Hz
Material	Polycarbonate: plastic part
Clamping Connection Capacity	1 x 23 mm ² for solid cable(s) 1 x 23 mm ² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	16.8 mm
Depth	28.3 mm

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 1 Height	8.7 cm	
De altra era di Milaldia		
Package 1 Width	8.7 cm	
Package 1 Length	2.83 cm	
	2.65 Cm	
Package 1 Weight	0.001 a	
r ackage r weight	0.001 g	

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations