Product datasheet

Specification





45A Double Pole Switch, White

E3031DR45_WW

Discontinued on: 23 Jan 2021

Main

Range	Neo	
Wiring Device Mounting	Flush	
	Surface	
Switch Function	2-pole	
Switch Application	Switch	
Load Type	Incandescent lamp	
	Inductive	
	Resistive	
Colour Tint	White	

Complementary

Rated Current	45 A at 250 V AC 50/60 Hz	
Material	Polycarbonate: plastic part	
Clamping Connection Capacity	1 x 23 mm² for solid cable(s) 1 x 23 mm² for stranded cable(s)	
Connections - Terminals	Pillar terminals	
Width	87 mm	
Height	87 mm	
Embedding Depth	16.8 mm	
Depth	28.3 mm	

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 1 Weight

Contractual warranty

Warranty

18 months

75 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information