Product datasheet

Specification





4A 1 Way Horizontal Bell Push Switch, White

E3031HBP_WW

Discontinued on: 20 Jun 2023

① Discontinued

Main

Range	Neo
Wiring Device Mounting	Surface Flush
Switch Function	Momentary
Switch Application	Bell
Load Type	Resistive
Bulb Type	Fluorescent (white)
Colour Tint	White

Complementary

Rated Current	4 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang horizontal
Material	Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s) 4 x 1.5 mm² for solid cable(s) 4 x 1.5 mm² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23 mm
Depth	36 mm

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1 GB 16915.1 EN 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

11 May 2024 Life Is On Schneider 1

Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	68 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	558 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6580 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations