# **Product datasheet**

Specification





# 600W 1 Gang Horizontal Dimming Switch with White LED, White

E3031HD\_EWWW

#### Main

Range	Neo C-Metro
Product Or Component Type	Dimmer
Bulb Type	LED, white
Number Of Gangs	1 gang
Colour Tint	White

### Complementary

Wiring Device Mounting	Flush Surface
Power Range	40600 VA incandescent lamp 40600 VA low voltage halogen lamp with electronic transformer
[Ue] Rated Operational Voltage	220240 V AC 50/60 Hz
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping Connection Capacity	1 x 4 mm² for stranded cable(s) 2 x 4 mm² for stranded cable(s) 1 x 2.5 mm² for solid cable(s) 1 x 2.5 mm² for stranded cable(s) 2 x 2.5 mm² for solid cable(s) 2 x 2.5 mm² for solid cable(s) 2 x 2.5 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	26 mm

#### **Environment**

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	GB 16915.2 IEC 60669-2-1

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 1 Height	21.0 cm	
Package 1 Width	32.5 cm	
Package 1 Length	50.0 cm	
Package 1 Weight	135.225 a	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations