Product datasheet

Specifications





4A Bell Push Switch w/Illuminated "DoNotDisturb&PleaseCleanUp" Sym., Grey Silver

E3031VBPDM_GS

Main

Range	Neo	
Product Or Component Type	Control switch	
Wiring Device Mounting	Flush Surface	
Switch Function	Momentary	
Switch Application	Bell	
Load Type	Inductive Resistive	
Colour Tint	Grey silver	

Complementary

•		
Rated Current	4 A at 250 V AC 50/60 Hz	
Number Of Gangs	1 gang vertical	
Material	Polycarbonate: plastic part	
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s) 4 x 1.5 mm² for solid cable(s) 4 x 1.5 mm² for stranded cable(s)	
Connections - Terminals	Pillar terminals	
Width	87 mm	
Height	87 mm	
Embedding Depth	23 mm	
Depth	36 mm	

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1
	EN 60669-1
	GB 16915.1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	68 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	558 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6580 g

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information