Product datasheet

Specifications





250V 20A Vertical Double pole switch Blue LED, Grey silver

E3031VD20-EBGS

! Discontinued on: 20 Jun 2023

Main

Range	Neo
Product Or Component Type	Control switch
Device Application	Control
Wiring Device Mounting	Surface Flush
Switch Function	2-pole
Switch Application	Switch
Load Type	Inductive Resistive Fluorescent lamp
Bulb Type	LED (blue)
Colour Tint	Grey silver

Complementary

Rated Current	20 A at 250 V AC 50 Hz	
Number Of Gangs	1 gang vertical	
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts	
Clamping Connection Capacity	1 x 2.51 x 6 mm² for solid cable(s) 1 x 2.51 x 6 mm² for stranded cable(s)	
Connections - Terminals	Pillar terminals	
Width	86 mm	
Height	86 mm	
Embedding Depth	19.7 mm	
Depth	8 mm	

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	GB 16915.1 EN 60669-1 IEC 60669-1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	8.6 cm
Package 1 Length	0.8 cm
Package 1 Weight	0.001 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations