

Product datasheet

Specifications



13A 250V 1 Gang Double Pole Switched RCD Socket

E8215DRC

Main

Range	Pieno
Product Or Component Type	Power socket-outlet
Device Application	Power supply
Switch Function	Switch
Rated Current	13 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Load Type	Resistive

Complementary

Wiring Device Mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	2 x 4 mm ² for stranded cable(s) 3 x 2.5 mm ² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	43 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS 7288

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	8.7 cm
Package 1 Length	4.3 cm
Package 1 Weight	0.001 g

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations