

# Product datasheet

Specifications



## 13A 250V 1Gang switched socket with Neon, Matt Black

E8215N\_MB\_G1

### Main

Range	Pieno
Product or component type	Power socket-outlet
Device application	Power supply
Switch function	Switch
Rated current	13 A at 250 V AC 50...60 Hz
Number of gangs	1 gang
Load type	Resistive
Cover frame colour tint	Matt black

### Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping connection capacity	2 x 4 mm <sup>2</sup> for stranded cable(s) 3 x 2.5 mm <sup>2</sup> for solid cable(s)
Width	87 mm
Height	87 mm
Depth	26.6 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	SS 145-2 BS 1363-2 MS 589-2

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.72 cm
Package 1 Width	8.7 cm

Package 1 Length	8.7 cm
Package 1 Weight	108.783 g
Unit Type of Package 2	CAR
Number of Units in Package 2	80
Package 2 Height	21 cm
Package 2 Width	32.5 cm
Package 2 Length	50 cm
Package 2 Weight	8702.64 g
Unit Type of Package 3	PAL
Number of Units in Package 3	1600
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	191052.8 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)