

# Product datasheet

Specifications



## 13A 250V 1 Gang Switched Socket with Neon, Full Red

E8215N\_RD

### Main

Product Or Component Type	Power socket-outlet
Switch Function	Switch
Rated Current	13 A at 250 V AC 50...60 Hz
Number Of Gangs	1 gang
Load Type	Resistive
Cover Frame Colour Tint	Red

### Complementary

Wiring Device Mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	2 x 4 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	26.6 mm

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	SS 145-2 BS 1363-2 MS 589-2

### Contractual warranty

Warranty	18 months
----------	-----------

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications