

Product datasheet

Specifications



13A 250V 1Gang switched socket, Matt Black

E8215_MB_G1

Main

Range	Pieno
Product or component type	Power socket-outlet
Device application	Power supply
Switch function	Switch
Rated current	13 A at 250 V AC 50...60 Hz
Number of gangs	1 gang
Load type	Resistive
Cover frame colour tint	Matt black

Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping connection capacity	2 x 4 mm ² for stranded cable(s) 3 x 2.5 mm ² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	26.6 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	BS 1363-2 SS 145-2 MS 589-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.72 cm
Package 1 Width	8.7 cm

Package 1 Length	8.7 cm
Package 1 Weight	107.983 g
Unit Type of Package 2	CAR
Number of Units in Package 2	80
Package 2 Height	21 cm
Package 2 Width	32.5 cm
Package 2 Length	50 cm
Package 2 Weight	8638.64 g
Unit Type of Package 3	PAL
Number of Units in Package 3	1600
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	189772.8 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)