



2Gang Blank Plate, Wine Gold

E8230TX_WG_G1

Main

Range	Pieno
Product Or Component Type	Blank plate
Number Of Gangs	2 gangs
Cover Frame Colour Tint	Wine gold

Complementary

Wiring Device Mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Width	87 mm
Height	147 mm
Depth	13.85 mm

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.385 cm
Package 1 Width	8.7 cm
Package 1 Length	14.7 cm
Package 1 Weight	98.846 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.0 cm
Package 2 Width	32.5 cm
Package 2 Length	50.0 cm
Package 2 Weight	9884.6 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	2000

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 3 Height	84.0 cm
Package 3 Width	82.5 cm
Package 3 Length	100.0 cm
Package 3 Weight	214692.0 a



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations