

Product datasheet

Specifications



Pieno - 16A 250V - 1 gang Intermediate switch with fluorescent locator (MB)

E8231MF_MB

Main

Range of product	Pieno
Product or component type	Switch
Switch function	Intermediate
Switch application	Switch
Rated current	16 AX at 250 V AC 50 Hz
Local signalling	Fluorescent (white)
Number of gangs	1 gang
Load type	Resistive Fluorescent

Complementary

Wiring device mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	Pillar terminals
Clamping connection capacity	2 x 1.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s)
Width	87 mm
Height	87 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 60669-1 GB 16915.1
Product certifications	CCC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.17 cm

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	107.91 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)