Product datasheet

Specifications





5W Volume control, 8 ohm

E8231VC-5

Main

Range	Pieno
Product Or Component Type	Volume control
Rated Operational Power In W	5 W

Complementary

Wiring Device Mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Average Impedance	8 Ohm
Width	87 mm
Height	87 mm
Depth	8.8 mm

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	8.7 cm
Package 1 Length	0.88 cm
Package 1 Weight	0.001 g

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations