

Product datasheet

Specifications



20A-16AX 250V 3 Gang 1 Way Switch with Fluorescent Locator, Aluminium Silver

E8233L1F20_AS_G1

Main

Range	Pieno
Product Or Component Type	Switch
Device Application	Control
Load Type	Resistive Fluorescent
Cover Frame Colour Tint	Aluminium silver

Complementary

Device Mounting	Flush Surface
Wiring Device Mounting	Surface Flush
Switch Function	1-way
Rated Current	20 A at 250 V AC 50 Hz
Local Signalling	Fluorescent (white)
Number Of Gangs	3 gangs
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	2 x 1.5 mm² for stranded cable(s) 2 x 2.5 mm² for solid cable(s)
Embedding Depth	23 mm
Width	87 mm
Height	87 mm
Depth	23 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	MS IEC 60669-1 IEC 60669-1 GB 16915.1 SS 227-1 BS EN 60669-1

Packing Units

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.55 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	128.49 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	80
Package 2 Height	21 cm
Package 2 Width	32.5 cm
Package 2 Length	50 cm
Package 2 Weight	10279.2 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	1600
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	222584 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations