Product datasheet





20A-16AX 250V 3 Gang 2 way switch with fluorescent locator, Matt Black

E8233L2F20_MB_G1

Main

Range	Pieno
Product Or Component Type	Switch
Device Application	Control
Load Type	Resistive Fluorescent
Cover Frame Colour Tint	Matt black

Complementary

o compromisme any		
Device Mounting	Flush Surface	
Wiring Device Mounting	Surface Flush	
Switch Function	2-way	
Rated Current	20 A at 250 V AC 50 Hz	
Local Signalling	Fluorescent (white)	
Number Of Gangs	3 gangs	
Material	Polycarbonate: surround Polycarbonate: grid plate	
Connections - Terminals	Pillar terminals	
Clamping Connection Capacity	2 x 1.5 mm² for stranded cable(s) 2 x 2.5 mm² for solid cable(s)	
Embedding Depth	23 mm	
Width	87 mm	
Height	87 mm	
Pepth 23 mm		

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	BS EN 60669-1 IEC 60669-1
	MS IEC 60669-1
	GB 16915.1
	SS 227-1

Packing Units

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.55 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	134.19 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	80
Package 2 Height	21 cm
Package 2 Width	32.5 cm
Package 2 Length	50 cm
Package 2 Weight	10735.2 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	1600
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	231704 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations