# **Product datasheet**

Specification





# 10AX 250V 4 Gang 1 Way Switch with Fluorescent Locator, Lavendar Silver

E8234L1F\_LS

#### Main

Range	Pieno	
Product Or Component Type	Switch	
Switch Application	Switch	
Load Type	Resistive Fluorescent	
Cover Frame Colour Tint	Lavender silver	

## Complementary

Device Mounting	Surface	
	Flush	
Wiring Device Mounting	Flush	
	Surface	
Switch Function	1-way	
Rated Current	10 AX at 250 V AC 50 Hz	
Local Signalling	Fluorescent (white)	
Number Of Gangs	4 gangs	
Material	Polycarbonate: surround	
	Polycarbonate: grid plate	
Connections - Terminals	Pillar terminals	
Clamping Connection Capacity	2 x 1.5 mm² for stranded cable(s)	
	2 x 2.5 mm² for solid cable(s)	
Embedding Depth	23 mm	
Width	87 mm	
Height	87 mm	
Depth	23 mm	

#### **Environment**

Ambient Air Temperature For Operation	-540 °C	
Relative Humidity	095 %	
Standards	MS IEC 60669-1	
	SS 227-1	
	BS EN 60669-1	
	GB 16915.1	
	IEC 60669-1	

## **Packing Units**

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	118.57 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	711.42 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	6897.6 g

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Reach Free Of Svhc	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations