Product datasheet

Specification



13A 250V 2Gang switched socket



E82T25

Main

Range	Pieno
Product Or Component Type	Socket-outlet
Device Application	Power supply
Switch Function	Switch
Rated Current	13 A at 250 V AC 5060 Hz
Number Of Gangs	2 gangs
Load Type	Resistive

Complementary

Wiring Device Mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	2 x 4 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s)
Width	147 mm
Height	87 mm
Depth	28.5 mm

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	SS 145-2
	MS 589-2
	BS 1363-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.7 cm
Package 1 Width	8.7 cm
Package 1 Length	2.85 cm
Package 1 Weight	0.001 g

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations