

Product datasheet

Specifications



13A 250V 2Gang switched socket with Neon

E82T25N

Main

Range	Pieno
Product or component type	Power socket-outlet
Device application	Power supply
Switch function	Switch
Rated current	13 A at 250 V AC 50...60 Hz
Number of gangs	2 gangs
Load type	Resistive

Complementary

Wiring device mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping connection capacity	2 x 4 mm ² for stranded cable(s) 3 x 2.5 mm ² for solid cable(s)
Width	147 mm
Height	87 mm
Depth	28.5 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	SS 145-2 BS 1363-2 MS 589-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.7 cm
Package 1 Width	8.7 cm
Package 1 Length	2.85 cm

Package 1 Weight 0.001 g

Offer Sustainability

Sustainable offer status Green Premium product

REACH Regulation [REACH Declaration](#)

REACH free of SVHC Yes

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Mercury free Yes

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

RoHS exemption information Yes

Environmental Disclosure [Product Environmental Profile](#)

Recommended replacement(s)