Product datasheet

Specifications





13A 250V 2Gang switched socket with Neon, Wine Gold

E82T25N_WG_G1

Main

Range	Pieno
Product Or Component Type	Power socket-outlet
Device Application	Power supply
Switch Function	Switch
Rated Current	13 A at 250 V AC 5060 Hz
Number Of Gangs	2 gangs
Load Type	Resistive
Cover Frame Colour Tint	Wine gold

Complementary

Wiring Device Mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	2 x 4 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s)
Width	147 mm
Height	87 mm
Depth	28.5 mm

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	BS 1363-2
	MS 589-2
	SS 145-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.85 cm
Package 1 Width	8.7 cm
Package 1 Length	14.7 cm
Package 1 Weight	188.218 g

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Unit Type Of Package 2	CAR
Number Of Units In Package 2	60
Package 2 Height	21 cm
Package 2 Width	32.5 cm
Package 2 Length	50 cm
Package 2 Weight	11293.08 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	1200
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	242861.6 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations