# **Product datasheet**

Specification





# 13A Twin Gang Switched Socket with 2.1A USB, Matt Black

E82T25USB\_MB\_G12

### Main

Range	Pieno	
Product Or Component Type	Power socket-outlet + USB charger	
Device Presentation	Mechanism	
Socket Additional Information	Shuttered	
Colour Tint	Matt black	
Load Type	No inductive load	

## Complementary

Socket Number	Number 1	
Device Mounting	Flush 47 mm	
Switch Function	ON/OFF power-socket outlet	
Number Of Power Socket Outlets	utlets 2 x 2P + E with shutters, British	
Rated Current	Power circuit: 13 A 220250 V, AC, 50/60 Hz	
Surface Finish	Glossy	
Surface Treatment	Painted	
Number Of Gangs	2 gangs	
Connector Type	USB type A	
[Ue] Rated Operational Voltage	220250 V AC 50/60 Hz	
laximum Power Consumption In 0.075 W		
Input Power	16 W	
Integrated Connection Type	2 USB port 5 V DC, maximum load current: 2.1 A	
Material	Polycarbonate: grid plate Polycarbonate: cover Polycarbonate: surround Polycarbonate: dolly Nylon + GF: shutter Brass: contact plate Steel: spring Nickel steel: terminal screw	
Protection Type	USB port: over temperature protection with PWM IC circuit USB port: over voltage protection against surges with PWM IC circuit USB port: overcurrent between output phases and earth (on power up only) with PWM IC circuit	
Shape Of Screw Head	Cross	
Screwdriver Shape	Philips	
Electrical Connection 3 screw terminal		

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Clamping Connection Capacity	1 x 4 mm² for solid cable(s)	
	2 x 4 mm² for stranded cable(s)	
	1 x 2.5 mm <sup>2</sup>	
	2 x 2.5 mm²	
Wire Stripping Length	1012 mm	
Mounting Support	Mounting box conforming to BS 4662	
Fixing Mode	By screws M3.5 x 25 mm	
Fixing Center	120.6 mm	
Product Compatibility	HTC	
, ,	Power bank	
	Smartphone	
	XiaoMi	
	Tablet PC	
	HW	
	Apple	
	Samsung	
Height	147 mm	
Width	87 mm	
Depth	38.6 mm	
Embedding Depth	ding Depth 29.5 mm	
Net Weight	0.166 kg	

## **Environment**

Operating Altitude	<= 2000 m
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	095 %
Standards	IEC 60950-1 BS 1363-2
Product Certifications	IEC
Ip Degree Of Protection	IP20
Environmental Characteristic	Alcohol Liquid soap

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	8.7 cm
Package 1 Length	14.7 cm
Package 1 Weight	171.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	5
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	905.0 g



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information