

Product datasheet

Specifications



Pieno - 115V/240V universal shaver Unit - vertical (MB)

E82T727V_MB

Main

Range of product	Pieno
Product or component type	Universal shaver
Installation direction	Vertical
Input voltage	240 V AC 50 Hz
Output voltage	115 V AC 50 Hz
Transformer rated power in VA	20 VA
Load type	Polarised Non-polarised

Complementary

Material	Polycarbonate: surround Polycarbonate: grid plate
Width	147 mm
Height	87 mm
Depth	49.7 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 61558-2-5

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	9.4 cm
Package 1 Length	15.5 cm
Package 1 Weight	599.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)