## **Product datasheet**

Specifications





# AvatarOn, push button for doorbell, 10A, 250V, LED, Wine Gold

E8331BPDMW\_WG

! Discontinued on: 20 Jun 2023



#### Main

Product Or Component Type	Push-button
Device Application	Doorbell
Colour Tint	Wine gold
Colour Tint	Wine gold

### Complementary

Device Presentation	Complete product	
Rated Current	10 A at 250 V AC 50/60 Hz	
Number Of Gangs	1 gang	
Number Of Rocker	1	
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s)	
Connections - Terminals	Brass terminal	
Local Signalling	On: LED indicator, LED (amber)	
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator	
Marking	DO NOT DISTURB Bell symbol Clean up symbol	
Device Mounting	Surface Flush	
Width	86 mm	
Height	86 mm	
Depth	33.5 mm	

#### **Environment**

Ip Degree Of Protection	IP20
Maximum Ambient Air Temperature For Operation	45 °C
Operating Altitude	2000 m
Relative Humidity	095 %
Environmental Characteristic	IIV recistant

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Standards SS 227-1

BS EN 60669-1 IEC 60669-1 MS IEC 60669-1

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	114.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.19 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations