Product datasheet

Specifications





45A CONNECTION UNIT

E84554_SZ

Discontinued on: 20 Jun 2023

Main

Product Or Component Type	Connection unit	
Load Type	Inductive Resistive	
Cover Frame Colour Tint	Silver bronze	

Complementary

Width	87 mm	
Height	87 mm	
Depth	30 mm	
Wiring Device Mounting	Surface Flush	
Rated Current	25 A at 250 V AC 50 Hz	
Material	Polycarbonate + 20 % FG: grid plate Polycarbonate: base Polycarbonate: surround	
Contacts Material	Contact: brass and phosphor bronze	
Connections - Terminals	Pillar terminals	
Number Of Cables	1 cable(s) 16 mm ²	

Environment

Ambient Air Temperature For Operation	-540 °C	
Relative Humidity	095 %	
Environmental Characteristic	al Characteristic UV resistant indoor use	
Operating Altitude	2000 m	
Standards	BS 5733	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	202.81 g

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.416 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	14668.6 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations