Product datasheet

Specifications





1 Gang, 13A 250V British Standard DP Switched Socket, Vivace, Small dolly, White

KB15D_WE

Main

Range	Vivace
Product Or Component Type	Switched socket
Device Short Name	KB15
Device Application	Power supply
Device Presentation	Complete product
Switch Application	On/off switching
Main Colour Tint	White
Colour Tint	White

Complementary

Outlet Poles Configuration	2P + E
Number Of Gangs	1 gang
Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	22.0 mm
Rated Current	13 A at 250 V AC, resistive
Network Frequency	50/60 Hz
Contacts Material	Brass and silver inlay
Connections - Terminals	4 screw terminals
Terminal Identifier	L N
Tightening Torque	2 N.m
Clamping Connection Capacity	1.54 mm ²
Width	86 mm
Height	86 mm
Depth	31.3 mm

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

Net Weight	
------------	--

Environment

Standards	BS 1363
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	095 %
Operating Altitude	<= 2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	93.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	744.0 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations