Product datasheet

Specifications





2 Gang Telephone Outlet with Shutter

KB32TS

Main

Range Of Product	Vivace
Range	Vivace
Device Short Name	KB32
Product Or Component Type	Telephone socket
Device Presentation	Complete product
Telephone Socket Type	RJ11 (8 contacts)
Colour Tint	Wall: white

Complementary

Number Of Gangs	2 gangs
Colour Tint	White
Connector Type	M-110 keystone 8 RJ11 connector
Material	Polycarbonate: surround Polycarbonate: grid plate Polycarbonate: base
Projecting Depth	8 mm
Type Of Cable	2 pairs
Device Mounting	Flush
Fixing Mode	By 2 screws
Mounting Support	Wall mounted
Fixing Center	60.3 mm
Surface Treatment	Untreated
Embedding Depth	28 mm
Surface Finish	Untreated
Telephone Socket Type	RJ11 (8 contacts)
Connections - Terminals	Clamp terminal
Tightening Torque	0.4 N.m
Width	87 mm
Height	87 mm
Depth	35 mm
Ip Degree Of Protection	IP20
Main Colour Tint	White

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Environment

Standards	IEC 60670-1
Ambient Air Temperature For Operation	-540 °C
Ambient Air Temperature For Storage	-540 °C
Relative Humidity	095 %
Operating Altitude	02000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	90.99 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	10 cm
Package 2 Weight	980 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	9349 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations