Product datasheet





Cover frame, Vivace, 1 gang, for switched and unswitched socket, light blue/grey

KB_01_BL

! Discontinued on: 22 Apr 2024

① Discontinued

Main

Range	Vivace	
Product Or Component Type	Cover frame	
Accessory / Separate Part Category	Fixing accessory	
Device Application	Wiring device adaptation	
Colour Tint	Wall: light blue/grey (Pantone 8220C)	

Complementary

Product Destination	Wiring device	
Fixing Mode	By clipping locks	
Range Compatibility	Vivace cover frame	
Number Of Gangs	1 gang	
Surface Finish	Painted	
Material	Polycarbonate: surround	
Surface Treatment	Painted	
Projecting Depth	8 mm	
Device Mounting	Flush	
Width	86 mm	
Height	86 mm	
Depth	8 mm	
Ip Degree Of Protection	IP20	

Environment

Standards	BS 5733
Ambient Air Temperature For Operation	-540 °C
Ambient Air Temperature For Storage	060 °C
Relative Humidity	095 %
Operating Altitude	02000 m
Environmental Characteristic	Indoor use

Packing Units

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	20 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	40
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	872 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	400
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8330 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations