# **Product datasheet**

Specifications





# Easypact CVS - CVS100B TM16D circuit breaker - 3P/3d

LV510300

#### Main

Range	EasyPact
Product Name	EasyPact CVS
Device Short Name	CVS100B
Product Or Component Type	Circuit breaker
Device Application	Distribution
Poles Description	3P
Protected Poles Description	3D
Earth Leakage Protection (Vigi Add On)	Without
[In] Rated Current	16 A at 40 °C
Network Type	AC
Utilisation Category	Category A
[Icu] Breaking Capacity	40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Rating	16 A at 40 °C
Protection Type	Short-circuit protection (magnetic) Overload protection (thermal)

#### Complementary

<u> </u>	
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to EN/IEC 60947-2
Network Frequency	50/60 Hz
Breaking Capacity Code	В
[Ics] Rated Service Breaking Capacity	15 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	30000 cycles
Electrical Durability	12000 cycles 415 V In conforming to IEC 60947-2
Control Type	Toggle
Thermal Protection Adjustment Range	11.216 A
Long Time Pick-Up Adjustment Type Ir	Adjustable
Long Time Pick-Up Adjustment Range	0.71 x ln

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

Long Time Delay Adjustment Type	Fixed
Instantaneous Pick-Up Adjustment Type Ii	Fixed
Instantaneous Pick-Up Adjustment Range	190 A
Contact Position Indicator	Yes
Mounting Mode	Fixed
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connections - Terminals	Screw connection
Connection Pitch	35 mm
Compatibility Code	CVS100
Width	105 mm
Depth	86 mm
Height	161 mm
Net Weight	1.5 kg

# Environment

Standards	IEC 60947-2 EN 60947-2
Product Certifications	IEC GOST
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

#### **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	14.000 cm
Package 1 Length	19.000 cm
Package 1 Weight	1.710 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	14.100 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	64

Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	124.800 kg

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free


Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

# **Product datasheet**


#### **Dimensions Drawings**





Туре	A	A1	A2	A3	A4	A/5	A6	A7	AS	A9	в	B1	B2	C1	C2	C3	E1
CV8100/160/250	86.5	161	64	148	170.5	155.5	236	169	226	250.5	52.5	105	146	-81	86	161@	62.5
C245400930	127.5	255	142.页	200	297	227.5	355	242.5	300	337	70	140	185	95.5	110	168	100
Type	E2	E3	E4	E5	E6	E7	E8	F1	F2	F3	G1	G2	G3	G4	G5	ØT	U
CARTERMER/250	125	61	140	137.5	200	148	215	22	17.5	70	20	78	13.6	25	17.5	24	y 32
CNS400830	200	113.5	222	299	300	2125	327	46	22.5	90	-		-		-	32	y 35


[8] C3=126mm Itr EasyPast CVS2500/F.

Assembly









Туре	A	A1	A2	A3	A4	A5	A6	A7	AS	A9	в	B1	B2	C1	C2	C3	E1
CV8100160/250	86.5	161	64	148	179.5	155.5	236	169	226	250.5	52.5	105	146	-81	86	181@	62.5
0245400/630	137.5	255	143.周	200	297	227.5	355	242.5	300	337	70	1-40	185	95-5	110	163	100
Type	E2	E3	E4	E5	E6	E7	<b>E8</b>	F1	F2	F3	G1	G2	G3	G4	G5	ØT	U
CWR100MG0/250	125	10	140	137.5	200	145	215	512	17.6	76	20	78	13.6	25	17.6	24	y 32
CV5400/850	200	113.5	222	200	300	213.5	327	45	22.5	90	-		-		-	32	y 35
Concession		100000	uterane	daruruz	C/0/0/	da 196552	Sareact		ulicilies 60*	10.00	-					0.0	7.0

(2) CJ=126mm Jor EasyPast CVS2500/F.

Performance Curves

