

Product datasheet

Specifications



Ulti - 250V 16 AX - 2 gang - 1 way
- impress switch module - blue
LED

U202SPM_1_B00

⚠ Discontinued on: 20 Jun 2023

⚠ Discontinued

Main

Range	Ulti
Device Application	Control
Product Or Component Type	Switch module
Load Type	Fluorescent
Switch Application	Switch

Complementary

Bulb Type	LED blue
Rated Current	16 AX at 250 V AC 50 Hz
Number Of Cables	3 cable(s) 2.5 mm²
Opening Distance	> 3 mm
Device Mounting	Flush
Fixing Mode	By screws
Distance Between Centers	60.3 mm
Number Of Gangs	2 gangs
Switch Function	1-way
Width	87 mm
Height	87 mm
Depth	23.3 mm

Environment

Ambient Air Temperature For Operation	0...35 °C
Relative Humidity	0...95 %
Standards	BS EN 60669-1
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.1 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.4 cm
Package 1 Length	8.6 cm
Package 1 Weight	171.45 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	18 cm
Package 2 Width	31.2 cm
Package 2 Length	56.3 cm
Package 2 Weight	5143.5 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	600
Package 3 Height	100 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	102870 g

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

<div>✓</div> Reach Free Of Svhc	
<div>✓</div> Mercury Free	
<div>✓</div> Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations