

Product datasheet

Specifications



Thorsman - TPP-10xM4 - cavity fixing - with screw - set of 1500

1200023

! Discontinued on: 30 Sept 2020

! End-of-service on: 26 Oct 2020

! Discontinued

Main

Range Of Product	Thorsman
Product Or Component Type	Cavity fixing
Device Short Name	TPP
Provided Equipment	Screw
Mounting Support	Board material - thickness: 10...30 mm
Device Application	10...26 mm board material
Mounting Support	Ceiling Wall mounted
Thread Type	M4
Screw Diameter	4 mm
Screw Length	55 mm
Drilling Diameter	10 mm
Colour Tint	Grey Metal

Complementary

Quantity Per Set	Set of 1500
Net Weight	0.0105 kg

Environment

Material	Screw: steel electroplated Toggle: zinc Collar: zinc Spring: steel
Practical Load Capacity	Shear: 400 N for 13 mm board 2.5) Pull-out load: 160 N for 13 mm board 3) Shear: 600 N for 2 x 13 mm board 2.5) Pull-out load: 220 N for 2 x 13 mm board 3)
Thickness	0...37 mm fixture 13 mm board 0...24 mm fixture 2 x 13 mm board
Ambient Air Temperature For Operation	-20...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	0.1 cm
Package 1 Width	0.1 cm
Package 1 Length	0.1 cm
Package 1 Weight	10 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations