

Product datasheet

Specifications



Multi9 - fuse-disconnector STI - 1 pole + N - 10 A - for fuse 8.5 x 31.5 mm

15645

⚠ Discontinued on: 2 May 2022

⚠ Discontinued

Main

Range	Multi9
Product Name	Multi9 STI
Product Or Component Type	Fuse-disconnector
Device Short Name	STI
Poles Description	1P + N

Complementary

[In] Rated Current	2 A 4 A 6 A 10 A
Fuse Curve	AM GG
Fuse Size	8.5 x 31.5 mm
[Ue] Rated Operational Voltage	400 V AC
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	75 mm
Colour	Grey
Connections - Terminals	Screw clamp terminals1 cable(s) 0.75...10 mm² rigid Screw clamp terminals1 cable(s) 0.33...6 mm² flexible
Tightening Torque	2 N.m

Environment

Standards	IEC EN 60947-3
Ip Degree Of Protection	IP20
Pollution Degree	3
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...80 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.075 kg

Contractual warranty

Warranty	18 months
----------	-----------