

Product datasheet

Specifications



current transformer TI 500/5 A - for straight busbar 64 x 11 mm

16473

⚠ Discontinued on: 17 Nov 2014

⚠ End-of-service on: 2 May 2023

⚠ Discontinued

Main

Range	PowerLogic
Product Name	CT
Product Or Component Type	Current transformer
Secondary Current	5 A
Accuracy Class	Class 0.5 at 2 VA Class 1 at 4 VA Class 3 at 6 VA
[In] Rated Current	500 A

Complementary

Current Transformer Type	Tropicalised for busbar
Current Transformer Ratio	500/5
Maximum Safety Factor	5
[Ue] Rated Operational Voltage	< 720 V AC 50/60 Hz
Mounting Mode	Insulated locking screw
Mounting Support	Mounting plate Busbar
Width	51 mm inner: 90 mm outside:
Height	130 mm outside: 31 mm inner:
Depth	66 mm outside:
Net Weight	0.5 kg
Opening Of Bars	64 x 11 51 x 31
Sealing	With

Environment

Standards	VDE 0414 IEC 60044-1
Product Certifications	CE
Ip Degree Of Protection	IP20
Relative Humidity	95...100 %
Ambient Air Temperature For Operation	-25...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------