

# Product datasheet

Specifications



## DPN - earth leakage circuit breaker - DPN N Vigi - 1P + N - 25A - 30mA

19667

⚠ Discontinued on: 1 Jan 2008

⚠ End-of-service on: 15 Dec 2019

⚠ Discontinued

### Main

Circuit Breaker Application	Distribution
Range	Multi9
Product Or Component Type	Earth leakage circuit breaker
Product Name	DPN Vigi
Device Short Name	DPN N Vigi
Poles Description	1P + N
Neutral Position	Left
[In] Rated Current	25 A at 30 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Earth-Leakage Sensitivity	30 mA
Earth-Leakage Protection Time Delay	Instantaneous
Type	Type AC
Breaking Capacity	6000 A Icn at 240 V AC conforming to EN 60898 6 kA Icn at 240 V AC conforming to EN 61009

### Complementary

Device Location In System	Outgoer
[Ue] Rated Operational Voltage	230 V AC
Magnetic Tripping Limit	5...10 x In
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Support	DIN rail
9 Mm Pitches	4
Net Weight	0.19 kg
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles conforming to IEC 61009
Connections - Terminals	Tunnel type terminals1 cable(s) 10 mm² flexible Tunnel type terminals1 cable(s) 16 mm² rigid

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Earth-Leakage Protection	Integrated
--------------------------	------------

## Environment

Standards	EN 60898 EN 61009
Tropicalisation	2
Relative Humidity	95 % at 55 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	8.5 cm
Package 1 Length	9 cm
Package 1 Weight	0.226 kg

## Contractual warranty

Warranty	18 months
----------	-----------