Product datasheet

Specifications





Standard opening undervoltage release MN, MasterPact NT, ComPacT NS630b/NS1600, drawout, 100/130VDC, 100/130VAC

33821

Main

Range	MasterPacT
Range Of Product	MasterPact NT
	MasterPact NT NAVY
	ComPacT NS630b1600 new generation
Device Short Name	MN
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Opening coil
	Undervoltage release
Control Type	Standard
[Uc] Control Circuit Voltage	100130 V AC 50/60 Hz
	100130 V DC
Circuit Breaker Mounting Mode	Drawout
Range Compatibility	Masterpact MasterPact NT
	ComPact ComPact NS630b1600

Complementary

Operating Threshold	0.350.7 x Un opening 0.85 x Un closing
Response Time	40 ms +/- 5 % for MasterPact NT 90 ms +/- 5 % for Compact NS630b1600
Supply Holding Power	4.5 VA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	8.0 cm
Package 1 Length	6.0 cm
Package 1 Weight	179.0 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information