# **Product datasheet**

Specifications





Pilot light head, Harmony 9001SK, plastic, without cap, 30mm, 220-240V

9001SKP7

#### Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for pilot light
Light Block Supply	Via transformer 220 V AC 50/60 Hz Via transformer 240 V AC 50/60 Hz

## Complementary

Bezel Material	Plastic
Mounting Diameter	30 mm
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Without cap
Bulb Base	BA 9s
Operating Mode	Normal
[Us] Rated Supply Voltage	220240 V
Light Block Supply	Via integral transformer
Supply Frequency	5060 Hz
Size	30 mm
Light Source	Incandescent bulb

#### Environment

Protective Treatment	TC
Ip Degree Of Protection	IP66

#### **Packing Units**

<u>~</u>	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.903 cm
Package 1 Width	5.08 cm
Package 1 Length	32.774 cm
Package 1 Weight	163.293 g

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information