Product datasheet

Specifications

Green Premium[™]



Acti9, Impulse relay iTLI - 2P -1NO+1NC - 16A - coil 110 VDC -230...240 VAC 50/60Hz

A9C30815

Main

mann	
Range Of Product	Acti9
Product Name	Acti9 iTL
Product Or Component Type	Impulse relay
Device Short Name	iTLi
Device Application	Changeover relay
Poles	2P
Pole Contact Composition	1 NO + 1 NC
[In] Rated Current	16 A
Network Type	AC
[Uc] Control Circuit Voltage	230240 V AC 50/60 Hz 110 V DC

Complementary

1 3	
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
Control Type	Coil deconnection Remote and manual control
Control Signal Type	Impulse
Switching Frequency	5 switching operations/minute 100 switching operations/day
Impulse Duration	50 ms1 s
Remote Control Type	Illuminated push-button 3 mA
Local Signalling	ON/OFF indication
Mounting Mode	Fixed
Mounting Support	DIN rail
9 Mm Pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Electrical Durability	AC-21: 200000 cycles AC-22: 100000 cycles

Life Is On Schneider

4 N
1 N.m
Acti 9 iATEt
Acti 9 iATL4
Acti 9 iATLc
Acti 9 iATLc+s
Acti 9 iATLm
Acti 9 iATLs
Acti 9 iATLz
Acti 9 iETL iTL 16
Acti 9 iATLc+c
Acti 9 iATL24

Environment

Standards	EN 669-1 EN 669-2-2
Product Certifications	CCC GOST
Quality Labels	CEBEC NF IMQ KEMA VDE
Noise Level	60 dB
Ip Degree Of Protection	IP20 conforming to IEC 60529 (on opening) IP40 conforming to IEC 60529 (in enclosure)
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2050 °C
Ambient Air Temperature For Storage	-4070 °C

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	1.700 cm
Package 1 Length	8.500 cm
Package 1 Weight	112.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.000 cm
Package 2 Width	9.100 cm
Package 2 Length	23.000 cm

Package 2 Weight	1.392 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	16.775 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations