

Acti9, comb busbar - 1L - 18 mm pitch - 24 modules - 100A



Main

| Range | Acti9 |
|---------------------------------------|----------------------|
| Product Or Component Type | Comb busbar |
| Mounting Mode | Horizontal |
| Accessory / Separate Part Category | Connection accessory |
| Lines Description | 1L |
| Length In 18 Mm Modules | 24 |

Complementary Number Of Ways

| Number Of Ways | 24 ways 1 L |
|--------------------------------|--|
| Poles Configuration For 1 Way | 1 x 1P |
| Connection Pitch | 18 mm |
| Connector Type | Tooth |
| Distance Between Way | 18 mm |
| Marking | L |
| Insulation | Insulated |
| Device Presentation | Cuttable |
| [le] Rated Operational Current | 100 A at 40 °C |
| [Ue] Rated Operational Voltage | 415 V AC |
| [Ui] Rated Insulation Voltage | 500 V AC conforming to IEC 61439-2 |
| Mounting Location | Top or bottom on tunnel type terminals Top or bottom on double terminal |
| 9 Mm Pitches | 48 |
| Width | 430 mm |
| Colour | White (RAL 9003) |
| Range Compatibility | Acti 9 Acti9 iC60 Acti 9 Acti9 iK60 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iSW Acti 9 Acti9 iSW Acti 9 Multi9 Multi9 C60 |

Environment

| Standards | IEC 60947-7-1 |
|-----------|---------------|
| | IEC 61439-2 |

| Fire Resistance | 960 °C (30 s) conforming to IEC 60695-2-1 |
|-------------------------|---|
| Pollution Degree | 3 conforming to IEC 60947-7-1 |
| Ip Degree Of Protection | IP20 with end-pieces and tooth covers |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1 cm |
| Package 1 Width | 3.1 cm |
| Package 1 Length | 43.2 cm |
| Package 1 Weight | 99.8 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 6.2 cm |
| Package 2 Width | 9 cm |
| Package 2 Length | 46.7 cm |
| Package 2 Weight | 1.118 kg |
| Unit Type Of Package 3 | S04 |
| Number Of Units In Package 3 | 100 |
| Package 3 Height | 30 cm |
| Package 3 Width | 40 cm |
| Package 3 Length | 60 cm |
| Package 3 Weight | 11.996 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ② | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| | Toxic Heavy Metal Free | |
| | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |