Product datasheet





network module, Modicon M340, EtherNet/IP and Modbus/TCP, 4 x **RJ45**

BMXNOC0401

Main

Range Of Product	Modicon M340 automation platform	
Product Or Component Type	Ethernet TCP/IP network module	
Concept	Transparent Ready	
Integrated Connection Type	e Ethernet RJ45 10/100 Mbit/s 4 twisted pairs transparent ready class B30	
Protective Treatment	TC	

Complementary

Communication Service	Bandwidth management
	Data Editor (via PC terminal)
	FDR server
	Rack Viewer
	SNMP network administrator
	Modbus TCP I/O Scanner and Messaging
	Ethernet/IP I/O Scanner and Messaging
	Embedded 4-port switch
	RSTP support
	Port mirroring
Port Ethernet	10BASE-T/100BASE-TX
Memory Usage	Application saving
	Activating the standard web server
Supply	Internal power supply via rack
Marking	CE
Local Signalling	1 LED (green) for processor running (RUN)
	1 LED (red) for processor or system fault (ERR)
	1 LED (amber) for status of Ethernet network (ETH STS)
	1 LED (green/red) for MS (Module Status)
	1 LED (green/red) for NS (Network Status)
Control Type	Processor or system fault (ERR)
Current Consumption	555 mA at 3.3 V DC
Module Format	Standard
Net Weight	0.2 kg

Environment

Ambient Air Temperature For Operation	060 °C
Relative Humidity	1095 % without condensation
Ip Degree Of Protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility 2014/34/EU - ATEX directive

Life Is On Schneider 20 May 2024

Product Certifications	CE	
	UL	
	CSA	
	RCM EAC Merchant Navy ATEX zone 2/22	
Standards		EN/IEC 61131-2
	EN/IEC 61010-2-201	
	UL 61010-2-201	
	CSA C22.2 No 61010-2-201	
	IACS E10	
	EN/IEC 61000-6-5, interface type 1 and type 2	
	EN/IEC 61850-3, location G	
	EN/IEC 60079-0	
Environmental Characteristic	Hazardous location class I division 2	

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	11.000 cm
Package 1 Length	12.000 cm
Package 1 Weight	219.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.656 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			
Circularity Profile	End of Life Information			

BMXNOC0401

Dimensions Drawings

Modules Mounted on Racks

Dimensions



- (1) With removable terminal block (cage, screw or spring).
- (2) With FCN connector.
- (3) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81