

Product datasheet

Specifications



multi-directional outdoor 3G/4G
antenna - 5 dBi -N connector - 5 m
of cable

EMS59160

Main

Range Of Product	PowerLogic T300
------------------	-----------------

Complementary

Product Or Component Type	Antenna
Connector Type	N

Environment

Mounting Location	Outdoor
Product Certifications	CE
Ik Degree Of Protection	IK07 conforming to IEC 62262
Relative Humidity	95 % conforming to IEC 60068-2-30
Ambient Air Temperature For Operation	-40...85 °C
Ambient Air Temperature For Storage	-40...85 °C
Fire Resistance	850 °C
Operating Altitude	3000 m
Height	40 mm
Width	150 mm
Length	390 mm
Net Weight	0.565 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.300 cm
Package 1 Width	21.500 cm
Package 1 Length	38.400 cm
Package 1 Weight	554.000 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	32
Package 2 Height	75.000 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	29.000 kg
------------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration