



Commercial status

Discontinued on: 21 December 2020

End-of-service on: 25 January 2021

HMIZGCAN has not been replaced. Please contact your customer care centre for more information.

⚠ Discontinued

Main

Range of product	Harmony GTU
Product or component type	CANopen slave unit

Complementary

Accessory / separate part destination	Universal panel
Power consumption in W	0.7 W
Input voltage	3.3 V DC
Range compatibility	Harmony GTU
Width	60 mm
Height	87 mm
Depth	41 mm
Net weight	0.1 kg

Environment

Ambient air temperature for operation	0...60 °C
Ambient air temperature for storage	-20...60 °C
Relative humidity	10...90 %
IP degree of protection	IP2
Vibration resistance	3.5 mm constant amplitude (f= 5...9 Hz) conforming to EN/IEC 61131-2 9.8 m/s ² (f= 9...150 Hz) conforming to EN/IEC 61131-2
Shock resistance	147 m/s ²
Product certifications	IEC-Ex KC CE EAC RCM ATEX zone 2/22

Packing Units

Package 1 Weight	80.000 g
Package 1 Height	66.000 mm
Package 1 width	90.000 mm

Package 1 Length	126.000 mm
------------------	------------

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
