Product datasheet





Straight length, Canalis KBA, 25A, 1 circuit, 3L+N+PE, compatible DALI, 2 outlets, 3m, white **RAL9003**

KBA25ED4302W

Main

| Range Of Product | Canalis |
|--------------------------------|------------------------------------|
| Device Short Name | КВА |
| Offer Type | Classic Control system |
| Product Or Component Type | Straight length |
| Busbar Description | Distribution length |
| Device Application | Lighting Power socket distribution |
| [le] Rated Operational Current | 25 A at 35 °C |
| [Ue] Rated Operational Voltage | 230400 V |
| Network Frequency | 50/60 Hz |
| Busbar Trunking Polarity | 3L + N + PE |
| Number Of Circuits | 1 |
| Number Of Tap-Off Outlets | 2 |
| Control Type | Communicating |
| Communication Port Protocol | DALI |
| Mounting Mode | By clips |

Complementary

| [Uimp] Rated Impulse Withstand Voltage | 4 kV |
|--|---|
| [Ui] Rated Insulation Voltage | 690 V |
| [Icw] Rated Short-Time Withstand Current | 0.44 kA |
| [lpk] Rated Peak Withstand Current | 4.4 kA |
| Thermal Stress Limit | 195 kA ² .s |
| Maximum Radiated Magnetic Field | 2 pT |
| Thdi | 015 % 25 A 1533 % 20 A 33100 % 16 A |
| Maximum Voltage Drop | <0.72 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.67 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.61 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.54 V with power factor = 0.7 at 50 Hz with 1A for 100 m long |
| Standards | EN/IEC 61439-6 EN/IEC 61439-1 |
| Width | 30 mm |

Life Is On Schneider 27 Apr 2024

| Height | 46 mm | |
|------------|------------------|--|
| Length | 3 m | |
| Colour | White (RAL 9003) | |
| Net Weight | 2.4 kg | |

Environment

| Ip Degree Of Protection | IP55 conforming to EN/IEC 60529 |
|---------------------------------------|--|
| Ik Degree Of Protection | IK06 conforming to EN/IEC 62262 |
| Ambient Air Temperature For Operation | 035 °C (100 % of In) 3540 °C (96 % of In) 4045 °C (93 % of In) 4550 °C (89 % of In) 5055 °C (85 % of In) |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.6 cm |
| Package 1 Width | 3.2 cm |
| Package 1 Length | 314 cm |
| Package 1 Weight | 3 kg |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 6 |
| Package 2 Height | 10.5 cm |
| Package 2 Width | 10.5 cm |
| Package 2 Length | 318.5 cm |
| Package 2 Weight | 18 kg |
| Unit Type Of Package 3 | PAL |
| Number Of Units In Package 3 | 144 |
| Package 3 Height | 53 cm |
| Package 3 Width | 64 cm |
| Package 3 Length | 320 cm |
| Package 3 Weight | 452 kg |
| | |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc |
|----------|--------------------------------|
| Ø | Toxic Heavy Metal Free |
| Ø | Mercury Free |
| Ø | Rohs Exemption Information Yes |
| ⊘ | Halogen Free Product |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |

Product datasheet

KBA25ED4302W

Dimension Drawings

